

DSKN insert holder, negative right

For facing with SN indexable insert



Application:

For facing with SN indexable insert, 90°

Execution:

- Precision-manufactured steel support, burnished, hardened, adjustable clamping system, type S, pitch angle 75°, tip angle 90°, clearance angle 0°

Advantage:

- Universal application for facing and longitudinal turning with high feed depths and unfavourable conditions
- Negative body geometry ensures good stability and absorption of force for large cutting depths
- Wide adjustment range: Suitable for both finishing and rough machining
- Adjustable clamp minimises vibrations and ensures favourable power transmission

Art. no.	17684 090
Brand	WIDIA
Manufacturer Part Number	5696688
ISO name	DSKN R/L 3232 P15
Knife edge length	15 mm
Shaft height	32 mm
Shank width	32 mm
Length	170 mm
Programming size	40 mm
Suitable for indexable inserts	SN.. 1906..
Tool design	Right
Length of head	32 mm
Gross Weight	1.362 kg
Product Group	1XG

EAN

4050841482967