

## Clamping heads, round version

**ORION®**

### Application:

Versatile in application, machining centres, all common axial force clamping systems on lathes and vices, measuring machines or pallet clamping.

### Execution:

- High-strength rubber/metal connection
- High retention forces
- Corrosion protection coating

|  |                  |
|--|------------------|
| <b>Art. no.</b>                          | <b>22001 061</b> |
| <b>Brand</b>                             | ORION            |
| <b>Manufacturer Part Number</b>          | 22001061         |
| <b>Size</b>                              | 42               |
| <b>Design</b>                            | Without stem     |
| <b>Profile shape</b>                     | Round and smooth |
| <b>Clamping diameter</b>                 | 4 mm             |
| <b>Length</b>                            | 42 mm            |
| <b>Min./max. clamping range diameter</b> | 3-42 mm          |
| <b>Gross Weight</b>                      | 0.910 kg         |
| <b>Product Group</b>                     | 2AO              |



### EAN

4053625466764