

Click-Torque torque wrench with reversible ratchet, adjustable

With calibration certificate, for clockwise tightening



Execution:

- setting: audible and perceptible click when scale values are reached
- release mechanism: audible and perceptible click signal when the set torque is reached
- very robust design, with ratchet (45 teeth)
- dual Nm and lbf-ft scale
- fine adjustment scale in Nm – ensures precise and safe operation
- ergonomically shaped 2-component handle
- locking button on the end of the handle with silicone padding – protection against unintentional adjustment



Delivery:

in a robust plastic rot. box

Art. no.	52261 295
Brand	WERA
Manufacturer Part Number	05075630001
Tip size	3/4 inch
Max. torque	1000 Nm
Min. torque	200 Nm
Scale value torque	1 Nm
Length	1250 mm
Min./max. torque	200-1000 Nm
Error limit (%)	3 %
Calibration certificate	Yes
Gross Weight	8.000 kg
Product Group	542

EAN

4013288193261