

Pneumatic impact screwdriver CP 721

Tightening torque 68 Nm



Application:

for heavy-duty screw-driving tasks.

Execution:

- clutch mechanism in oil bath
- Integrated power regulator

Advantage:

- clutch provides consistent operation and extremely long service life

Delivery:

In cardboard box



Art. no.	75066 007
Brand	CP
Manufacturer Part Number	T021963
Model	CP721
Max. tightening torque	650 Nm
Max. idle speed	11000 rpm
Air consumption	300 l/min
Tool holding device	3/8-inch external square
Hammer mechanism system	Rocking-Dog striking mechanism
Length	146 mm
Connection thread	G 1/4 inch
Inner hose diameter	8 mm
Sound-pressure level	87
Weight	1.2 kg
With right/left-hand rotation	Yes
Gross Weight	1.440 kg
Product Group	752

EAN

0015451219635