



# Trueforce Core LED SON-T

## TForce Core LED road 26W 740 E27 MV

The new Philips Trueforce Core LED SON-T lamps offer you an easy, short-payback LED solution to replace High Intensity Discharge (HID) lamps. This new generation of products brings all the energy-efficiency and long-lifetime benefits of LED to HID replacement, while providing instant saving with a low initial investment. Furthermore, they're designed to have the same lamp size and light distribution as other HID lamps, so you will never know the difference. All thanks to our High-Power LED filament technology. Plus, its unique IP65 design means it can be used for outdoor applications.

### Product data

General information		Operating and electrical	
Cap-Base	E27 [ E27]	Input Frequency	50 to 60 Hz
EU RoHS compliant	Yes	Power (Nom)	26 W
Nominal Lifetime (Nom)	25000 h	Lamp Current (Nom)	120 mA
Switching Cycle	15000X	Wattage Equivalent	70 W
Flux measurement reference	Sphere	Starting Time (Nom)	0.5 s
		Warm Up Time to 60% Light (Nom)	0.5 s
		Power Factor (Nom)	0.9
		Voltage (Nom)	220-240 V
Light technical		Temperature	
Color Code	740 [ CCT of 4000K]	T-Case Maximum (Nom)	66.4 °C
Luminous Flux (Nom)	4500 lm		
Color Designation	Cool White (CW)	Controls and dimming	
Correlated Color Temperature (Nom)	4000 K	Dimmable	No
Luminous Efficacy (rated) (Nom)	173.00 lm/W		
Color Consistency	<6		
Color Rendering Index (Nom)	70		
LLMF At End Of Nominal Lifetime (Nom)	70 %		

# Trueforce Core LED SON-T

## Mechanical and housing

Bulb Finish	Clear
Bulb Shape	T-shape

## Approval and application


Energy Efficiency Class	C
Energy Consumption kWh/1000 h	26 kWh
EPREL Registration Number	574358

## Product data

Full product code	871951431631700
-------------------	-----------------

Order product name	TForce Core LED road 26W 740 E27 MV
EAN/UPC - Product	8719514316317
Order code	929002485102
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	929002485102
Net Weight (Piece)	0.100 kg


## Dimensional drawing




TForce Core LED road 26W 740 E27 MV

Product	D	C
TForce Core LED road 26W 740 E27 MV	38 mm	210 mm

## Photometric data




LEDTForce Core road 26W Tshape E27 740-POC



LEDTForce Core road 17W Tshape E27-LDD


# Trueforce Core LED SON-T

## Photometric data




LEDTrueforce Core road 26W Tshape E27 740-GUL

## Lifetime



LEDspots LED 25K



LEDspots LMP 25K

