
KEMET Part Number: C410C104K5R5TA91707200



AxiMax 400 Auto X7R, Ceramic, 0.1 uF, 10%, 50 VDC, X7R, AxiMax, Automotive Grade



Dimensions		
D	2.41mm MAX	
L	4.32mm MAX	
LL	25.4mm MIN	
F	0.51mm +0.025/-0.076mm	

Packaging Specifications		
Packaging:	T&R, 305mm	
Packaging Quantity:	5000	

General Information	
Supplier:	KEMET
Series:	AxiMax 400 Auto X7R
Description:	AxiMax, Automotive Grade
Features:	Automotive Grade
RoHS:	Yes
Termination:	Tin
Failure Rate:	N/A
Qualifications:	AEC-Q200
AEC-Q200:	Yes
Halogen Free:	Yes

Specifications		
Capacitance:	0.1 uF	
Capacitance Tolerance:	10%	
Voltage DC:	50 VDC	
Dielectric Withstanding Voltage:	125 VDC	
Temperature Range:	-55/+125C	
Temperature Coefficient:	X7R	
Dissipation Factor:	2.50% 25C	
Aging Rate:	3% Loss/Decade Hour	
Insulation Resistance:	10 GOhms	

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

