




ESTGH050ZDS00.5E05 (PG9)

Connection technology



1: O-ring

Product characteristics

Adapter plug

M12 connector

PG 9 - M12

Electrical data

Electrical design

AC/DC

Operating voltage [V]

125 AC/DC

Environment

Ambient temperature [°C]

-20...85

Protection

IP 68

Mechanical data

Design

straight

Housing materials

diecast zinc

Weight [kg]

0.02

Electrical connection

Connection

PVC cable / 0.5 m; 4 x 0.25 mm<sup>2</sup> + 1 x 0.5 mm<sup>2</sup>

**Wiring**

Core colours


BK black

BN brown

BU blue

GN/YE green/yellow

WH white



1 BN

2 WH

3 BU

4 BK

5 GN/YE

Remarks

Pack quantity

[piece]

1