




Datenblatt - Fiche technique - Data sheet


**21.15.2531**



ROLINE Patchkabel Kat.6 UTP, Component Level, LSOH, grün, 1,0 m

Cordon ROLINE UTP Cat.6, LSOH, Component Level, vert, 1,0 m

ROLINE UTP Cable Cat.6 Component Level, LSOH, green, 1.0 m



**1. ELECTRICAL TEST:**

- (1). 100% OPEN SHORT & MISS WIRE TEST;
- (2). INSULATION RESISTANCE:DC 250V 20M OHM MIN;
- (3). CONTACTOR RESISTANCE:30 OHM MAX

2. PRINTING:GHMT® roline CAT.6 U/UTP COMPONENT PATCH CORD LSZH 250MHz ISO/IEC 11801 & EN 50173-1 & ANSI/TIA-568-C.2

- 3. 100% Component Patch cord Test PASS
- 4. Minimum bending radius:50mm

**MATERIAL LIST**

⑥	LABEL	NO DRY GLUE LABEL	1PCS	
⑤	MINI TIE	PE MINI TIE (POSSESS METAL)	2PCS	
④	POLYETHYLENE BAG	POLYETHYLENE BAG	1PCS	
③	OVER MOLD	88A PVC Green	2PCS	
②	CONNECTOR	RJ45 8P8C' S UNSHIELDED PIN GOLD PLATED 3u", Transparent RED	2PCS	
①	CABLE	U/UTP CAT.6 24AWG (BC*1P)*4+CROSS + JACKET LSOH OD=6.0±0.2MM	1PCS	
NO.	PARTS NAME	SPECIFICATION STANDARD	QT' Y	REMARK

COLOUR:Green (PANTONE:3278C)		
ITEM NO.	LENGTH (L)	TOLERANCE (T)
21. 15. 2943	300mm	±10mm
21. 15. 2530	500mm	±15mm
21. 15. 2531	1000mm	±30mm
21. 15. 2534	1500mm	±45mm
21. 15. 2532	2000mm	±60mm
21. 15. 2533	3000mm	±90mm
21. 15. 2535	5000mm	±150mm
21. 15. 2536	7500mm	±210mm
21. 15. 2537	10000mm	±300mm
21. 15. 2538	15000mm	±450mm
21. 15. 2539	20000mm	±600mm

ITEM NO.	21. 15. 2943	21. 15. 2530	21. 15. 2531	21. 15. 2532	21. 15. 2533
21. 15. 2534	21. 15. 2535	21. 15. 2536	21. 15. 2537	21. 15. 2538	21. 15. 2539
DESC.	ROLINE UTP PatchCord CAT. 6, LSOH, Comp. Level, Green				

		NEW	2016-10-20	A
BY	CHK	REVISION RECORD MODIFICATIONS	DATE	REV.

SECOMP