HAKKO FX-888

Solutions for the variety of needs from the field.

Addition of shapes to T18 series offers you more applications for a variety of operations.



New Lineup for HAKKO FX-888

T18 Series

HAK(0FX-8801 歸

With addition of 11 shapes, T18 series offers you wider lineup than 900M series. There will be the right tip for a variety of operations.

(Please see reverse for the details.)



N2 System Soldering Iron

N2 system iron heats up Nitrogen gas inside the iron and provides "antioxidant effect" and "preheating effect" by blowing the hot Nitrogen gas out of the top of the iron. These effects can reduce the incidence of solder bridges, icicles, and unwettability. And this is suitable for lead-free soldering with low activated flux and soldering on multilayered PWB.

(Please see reverse for the lineup of tips.)

*HAKKO FX-888 iron holder can be used if supplied Nitrogen guard (B3661) is used.

Model Name	HAKKO FX-8802	
Power Consumption	AC26V 65W	
Tip to Ground Resistance	<2Ω	
Tip to Ground Potential	<2mV	
Standard Tip	T18-B (Type B)	
Temperature Range	200 to 480°C	
Cord	1.2m	
Total Length (w/o cord)	190mm with B tip	
Weight (w/o cord)	59g with nozzle assembly A and B tip	



Soldering Gun

It enables to feed and heat solder at the same time with a single hand and the other hand is free to hold PWB. Manual feeding system can help beginners keep their operation pace and is suitable for cell production system.



(Please see reverse for the lineup of tips.) *Requires separate purchase of iron holder (C1437)

HAKKO FX-8803	
AC26V 65W	
<2Ω	
<2mV	
T18-CF3 (Shape 3C, cut surface only)	
200 to 480°C	
ø1.0	
ø0.6, 0.8, 1.0, 1.2, 1.6	
1.1m	
170(W) X 180(H) X 23(D)mm	
207g with T18-CF3 tip	



SMD Hot Tweezers


The hot tweezers make it easy to remove CHIP and SOP components. Unlike hot air system, its direct heating system minimizes thermal affect to components around. And addition of 2 more new size (A1576/2.6C, A1577/0.5L) for CHIP components to the conventional model of HAKKO 950 makes the lineup of tips greater than ever.

*Requires purchase of optional part (B3666 holder clip) for use with iron holder for HAKKO FX-888.

Model Name	HAKKO FX-8804	
Power Consumption	AC26V 65W	
Tip to Ground Resistance	<2Ω	
Tip to Ground Potential	<2mV	
Standard Tip	A1378 (tip for chip 2L)	
Temperature Range	200 to 400°C	
Cord	1.2m	
Total Length (w/o cord)	186mm	
Weight (w/o cord)	93g (with tip for chip 2L)	



Tips for HAKKO FX-8801/FX-8802/FX-8803



Tips for HAKKO FX-8804

For Chip Component

Part Number	Part Name	Size of A (B)	Tip Shape
NEW A1577	Tip/CHIP 0.5L	0.5 mm	
A1379	Tip/CHIP 1L	1 mm	A
A1378	Tip/CHIP 2L	2 mm	
A1388	Tip/CHIP 0.5C	1.5(0.5)mm	A B 45°
A1389	Tip/CHIP 0.5I	R0.25 mm	A A
NEW A1576	Tip/CHIP 2.6C	2.6 mm	A + 45°

For SOP Component

Part Number	Part Name	Size of A (B)	Tip Shape
A1390	Tip/SOP 4L	4 mm	~ <i>x</i> 0
A1391	Tip/SOP 6L	6 mm	
A1380	Tip/SOP 8L	8 mm	
A1381	Tip/SOP 10L	10 mm	
A1382	Tip/SOP 13L	13 mm	
A1392	Tip/SOP 15L	15 mm	<u> </u>
A1383	Tip/SOP 18L	18 mm	A ¶/
A1384	Tip/SOP 20L	20 mm	
A1385	Tip/SOP 25L	25 mm	<u>†</u>
			_

CA00365EbZa001 2011.2

สอบถามรายละเอียดเพิ่มเติมได้ที่ มีจำหน่ายตามร้านอะไหล่อิเล็กทรอนิกส์ทั่วไป บริษัท สหรุ่งโรจน์ (ประเทศไทย) จำกัด

1034 ถนนเจริญนคร แขวงบางลำภูลาง เขตคลองสาน กรุงเทพฯ 10600 โทร. (02) 438-7783 (อัตโนมัติ) แฟ็กซ์. (02) 438-4166, 862-6740 http://www.srt.co.th E-mail. srtcoltd@anet.net.th

srthe02@truemail.co.th

แผนกต่างจังหวัด และ พุกงุ. กรุณาติดต่อสาขาวัดตึก

โทร. (02) 225-7076 แฟ็กซ์. (02) 225-2979

สาขาวัดตึก 67,69,71,73 ถนนจักรวรรดิ์ แขวง/เขตสัมพันธวงศ[์] กรุงเทพฯ 10100

โทร. (02) 225-7070 (อัตโนมัติ), 622-7311-5

แฟ็กซ์. (02) 225-2979, 222-0052

E-mail. srtcoltd@anet.net.th srtwt02@truemail.co.th