




Order Code	TCK-062
Inductance	12 μ H \pm 20% (at 1 kHz / 300 mV)
Impedance (DCR)	120 mOhm max.
Rated Current	1.4 A max.
Operating Temperature	-40°C to +125°C



Impedance Curve



Outline Dimensions



Dimensions [mm]	
A	5.2 \pm 0.5
B	5.8 \pm 0.5
C	5.2 max.
D	1.3 typ.
E	5.5
F	2.15
G	1.7

