

## Multimar universal measuring device

Mahr

### Application:

For universal measurements of diverse tasks, e.g. external and internal measurement of bores, threads, tothing, recesses, grooves etc.

### Execution:

- Direction of the measuring force can be changed for measuring external or internal dimensions
- Integral measuring force spring to ensure a constant measuring force
- The movable measuring arm holder is housed in a high-precision ball-bearing guide to minimise play and friction
- Strong, ground, hard chrome-plated column
- Mount for dial gauges and precision pointers,  $\varnothing$  8 mm

### Delivery:

Operating instructions, assembly and storage blocks, wooden box (without display unit, gauge slides)



<b>Art. no.</b>	<b>31900 205</b>
<b>Brand</b>	MAHR
<b>Manufacturer Part Number</b>	4503002
<b>Min./max. external length measuring range</b>	80-235 mm
<b>Min./max internal length measuring range</b>	110-265 mm
<b>Measuring span</b>	12 mm
<b>Measurement force</b>	5 N
<b>Gross Weight</b>	3.500 kg
<b>Product Group</b>	305

### EAN

4059192024901