

MHL


- For Blacklight Special Effects
- Only Use in UV Protective Housing!

Please see Safety and Handling Instructions on page 81.




Watts	Ushio Ordering Code	Ushio Lamp Description	Volts V	Spectral Range	Dimensions mm			Arc Length (D)	Avg Life h	Base Type
					Dia (A)	MOL (B)	LCL (C)			
Single Ended Metal Halide - G12 Base										
70	5001468	MHL-70	95	300-450nm	23.0	102	56	—	500	G12
150	5001381	MHL-150	95	300-450nm	23.0	102	56	—	500	G12
Double Ended Metal Halide										
250	5000089	MHL-250	125	300-450nm	15.5	68	—	15.5	500	RSC
450	5000114	MHL-450	140	300-450nm	16.3	105	—	31.0	500	RSC
1200	5000061	MHL-1000	120	400-450nm	25.0	130	—	24.0	500	Ceramic Base w/AMP Connector
1200	5000062	MHL-1000/1	135	350-370nm	23.0	147	—	68.0	500	RSC

70W & 150W




G12

250W



R7s

450W, 600W & 1200W



R7s

(Hg) - LAMP CONTAINS MERCURY
 Manage in Accord with Disposal Laws
 See: www.lamprecycle.org