

GN 273-NI | Pivoting connecting clamps

Stainless steel



- 1
- 2
- 3
- 4
- 5
- 6
- 7
- 8
- 9
- 10
- 11
- 12
- 13
- 14
- 15
- 16
- 17
- 18**
-

MATERIAL




Cast AISI CF-8 stainless steel, sandblasted matte finish.
AISI 304 stainless steel screw and nut.

FEATURES AND APPLICATIONS

The assembly hole of GN 273-NI connecting clamps allows an excellent match with tubes GN 990 (see page 1778).

GN 273-NI bases can be assembled with pivoting connecting clamps GN 271-NI (see page 1751), GN 275-NI (see page 1756) or GN 277-NI (see page 1757).

The clamping screw d3 may be replaced by clamping kit GN 911 (see page 1782).



Code	Description	b	d1	d2	d3	d4	k	l	m	t	s	d3 Clamping kit	
GN.57413	GN 273-B12-2-NI	25	12	6.5	M6	M6	25	64	29.5	12.5	10	GN 911-M6-22	156
GN.57433	GN 273-B14-2-NI	25	14	6.5	M6	M6	25	64	29.5	12.5	10	GN 911-M6-22	149
GN.57443	GN 273-B15-2-NI	25	15	6.5	M6	M6	25	64	29.5	12.5	10	GN 911-M6-22	147
GN.57453	GN 273-B16-2-NI	25	16	6.5	M6	M6	25	64	29.5	12.5	10	GN 911-M6-22	143
GN.57473	GN 273-B18-2-NI	25	18	6.5	M6	M6	25	64	29.5	12.5	10	GN 911-M6-22	135
GN.57483	GN 273-B20-2-NI	25	20	6.5	M6	M6	25	64	29.5	12.5	10	GN 911-M6-22	126

Connecting clamps