



Figure can vary

Part no.: 529615
UM60-1500
Deflecting mirror

Contents

- Technical data
- Dimensioned drawings

Part no.: 529615 – UM60-1500 – Deflecting mirror

Technical data

Basic data

Series	UM
Type, columns and mirrors	Deflecting mirror

Mechanical data

Dimension (W x H x L)	25 mm x 68 mm x 1,570 mm
Net weight	2,820 g
Housing color	Yellow, RAL 1021
Type of fastening	Groove mounting Swivel mount
Suitable for sensor	MLC 500, MLC 300 safety light curtains
Protected field height up to	1,500 mm
Mirror length	1,560 mm


Classification

Customs tariff number	70099200
eCl@ss 8.0	27279207
eCl@ss 9.0	27273605
ETIM 5.0	EC002467
ETIM 6.0	EC002467

Dimensioned drawings


All dimensions in millimeters

Mirror




L Length = 1570 mm
 SL Mirror length = 1560 mm

Mounting distances




A Max. 500 mm

Mounting with BT-UM60 standard bracket



A Lateral
 B Rear side
 C Adjustable at an angle (0 - 90°)

Mounting with BT-SSD swiveling mounting bracket



A Rear side
 B Lateral 45°