

TCG-4880X07-1



Specifications & Features

Dimensions (WxDxH) : 482.6 x 688 x 176.8 (mm), (19" x 27.1" x 7.0")

Drive bays : 8x 5.25" exposed drives

Mainboard Type : Extended ATX (12" x 13")

Cooling : 3 x 120mm + 1 x 80mm Ball Bearing Fans (Standard)

Switches : Power ON/OFF, System & Alarm Reset

Indicators : LEDs for Power ON/OFF, HDD, Fan & Alarm

Slot Opening : 7 Slots

Air Filter : removable & washable

Security : Both Front Doors Are Lockable

Speaker : 0.4W Built-In

Fan Control :(optional) Fan temperature detecting board for system environment monitoring

Material of Front Bezel : Aluminum alloy With Hard anodized treatment

Material of Handle : Aluminum alloy

Material of Main Chassis : 1.2mm SECC Zinc-coated steel (Japan Made)

colour of front bezel : black

colour of main chassis : black

Power Supply (PSU) : PS2 size or Mini Red. ATX or EPS 2x 300W/ 2x 400W/ 2x500W power supply

TC-300P ATX 300W power supply w/ PFC/CE/TUV/UL

TC-400P ATX 400W power supply w/ PFC /CE/TUV/UL

TC-300R8 Mini Red. ATX 2x 300W power w/ PFC/CE/TUV/ UL

TC-400R8 Mini Red. ATX 2x 400W power w/ PFC/CE/TUV/UL

TC-300R8A Mini Red. EPS 2x 300W power w/ PFC/CE/TUV/ UL

TC-400R8A Mini Red. EPS 2x 400W power w/ PFC/CE/TUV/UL

TC-500R8A Mini Red. EPS 2x 500W power w/ PFC/CE/TUV/ UL

Extra Optional parts : 19" Sliding Rail : TC-SR26W 1x pair 26" Sliding rail with 4 x metal bracket for easy installation the 19" chassis into each 19" Cabinet

Packing Data

Measurements (WxDxH) : 540 x 825 x 280 (mm),(21.3" x 32.5" x 11.0")

Cubic Feet Of Packing : 4.4' (Cuft)

Net Weight : 15.0Kgs (w/o PSU), 17.08Kgs (w/PSU)

Gross Weight : 18.6Kgs (w/o PSU), 20.6Kgs (w/PSU)