

# Neodymium shallow pot datasheet

## Internal thread

- Zinc plated body
- With threaded stem
- 80° max operating temp



### Product Information

Product Number	Diameter mm	Thickness* mm	Thread mm	Weight kg	Pull Force kg	Units / Pack
E1018/NEO	10	4.5	M3	0.0025	1.0	20
E1019/NEO	13	4.5	M3	0.0043	2.5	20
E1020/NEO	16	4.5	M4	0.0063	5.0	20
E1021/NEO	20	6	M4	0.011	7.0	10
E1022/NEO	25	7	M5	0.021	13.5	10
E1023/NEO	32	7	M6	0.036	25.0	10
E1024/NEO	40	8	M6	0.068	39.0	5

