



Heat Shrinkable Tubing 2:1 flexible and transparent

TF24

Protects wire and cable markers subject to abuse, while permitting inspectability of each item covered. Protects electronic components while permitting their identification and inspection.

Features and Benefits

- Transparent, flexible polyolefin tubing
- Protects identification marking perfect
- Halogen free
- Good mechanical and chemical resistance
- VG-approval and additional industrial approvals



TF24 transparent tubing with 2:1 shrink ratio.



Cut lengths available on request. Please contact us!



One Step to the Web!

| | |
|--|---|
| MATERIAL | Polyolefin, cross-linked (PO-X) |
| Shrink Ratio | 2:1 |
| Operating Temperature | -55 °C to +135 °C |
| Minimum Shrink Temperature | +110 °C |
| Longitudinal change after shrinkage | +/-5 % max. |
| Dielectric Strength | ≥ 30 kV/mm min. according to ASTM D2171 |
| Flammability | not flame retarded |
| Specifications | DEF STAN 59-97 Type 2B, SAE - AMS - DTL-23053/5 Class 2, VG 95343 |



| TYPE | Supplied Ø D min. | Size (imperial) | Recov. Ø d max. | Wall (WT) | Reel Length | Colour | Designation as per VG-Norm | Article-No. |
|-----------------|-------------------|-----------------|-----------------|-----------|-------------|------------------|----------------------------|-------------|
| TF24-1.2/0.6 | 1.2 | 3/64 " | 0.6 | 0.41 | 100 m | Transparent (CL) | VG95343T05B001M | 309-40123 |
| TF24-1.6/0.8 | 1.6 | 1/16 " | 0.8 | 0.43 | 100 m | Transparent (CL) | VG95343T05B002M | 309-40163 |
| TF24-2.4/1.2 | 2.4 | 3/32 " | 1.2 | 0.51 | 100 m | Transparent (CL) | VG95343T05B003M | 309-40243 |
| TF24-3.2/1.6 | 3.2 | 1/8 " | 1.6 | 0.51 | 100 m | Transparent (CL) | VG95343T05B004M | 309-40323 |
| TF24-4.8/2.4 | 4.8 | 3/16 " | 2.4 | 0.51 | 60 m | Transparent (CL) | VG95343T05B005M | 309-50483 |
| TF24-6.4/3.2 | 6.4 | 1/4 " | 3.2 | 0.64 | 60 m | Transparent (CL) | VG95343T05B006M | 309-50643 |
| TF24-9.5/4.8 | 9.5 | 3/8 " | 4.8 | 0.64 | 50 m | Transparent (CL) | VG95343T05B007M | 309-40953 |
| TF24-12.7/6.4 | 12.7 | 1/2 " | 6.4 | 0.64 | 50 m | Transparent (CL) | VG95343T05B008M | 309-41273 |
| TF24-19.1/9.5 | 19.1 | 3/4 " | 9.5 | 0.76 | 50 m | Transparent (CL) | VG95343T05B009M | 309-31903 |
| TF24-25.4/12.7 | 25.4 | 1 " | 12.7 | 0.89 | 50 m | Transparent (CL) | VG95343T05B010M | 309-32543 |
| TF24-38.1/19.1 | 38.1 | 1-1/2 " | 19.1 | 1.02 | 60 m | Transparent (CL) | VG95343T05B011M | 309-33813 |
| TF24-50.8/25.4 | 50.8 | 2 " | 25.4 | 1.14 | 60 m | Transparent (CL) | VG95343T05B012M | 309-35083 |
| TF24-76.2/38.1 | 76.2 | 3 " | 38.1 | 1.27 | 30 m | Transparent (CL) | VG95343T05B013M | 309-37603 |
| TF24-101.6/50.8 | 101.6 | 4 " | 50.8 | 1.40 | 15 m | Transparent (CL) | VG95343T05B014M | 309-31023 |

All dimensions in mm. Subject to technical changes.
Minimum Order Quantity (MOQ) may differ from package content.



For product specific approvals and specifications please refer to the Appendix.