


ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED


WITHOUT	THE	EXPRESS	WRITTEN	CONSENT	OF	SPC	
TECHNOL	OGY.						


SPC-F005.DWG


	REVISIONS			DOC. NO. SPC-F005 * Effective: 7/8/02 * DCP No: 1398					
DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE	
1876	Α	RELEASED	EO	03/21/06	TL	05/15/06	но	05/15/06	













· 47.0 [1.85] –

⊷ 34.0 [1.339] –

FRONT VIEW OF 8P8C TELEPHONE JACK (W/KEYED TYPE)



WIRE SYSTEM: 1 2 3 5 6 BLU ORG BLK RED GEN YEL BRO GRY(WHT)





- D-Sub Connector: Tin-Plated Shell with Black Color Insulator

- Contact:

a- D-Sub: Brass, Gold-Plated b- RJ45: Brass, Gold-Plated

Body: ABS

- Thumb Screw: Steel, Nickel-plated

- Electronic Wire: UL1061, 26AWG

						_
	E	00000]		16.0	† [0.63] <u>↓</u>
-	— 55.0	0 [2.165] —	-		

11.3 [0.445] -

PART NO.	COLOR
SPC15464	BLACK
SPC15279	BLUE
SPC15222	RED
SPC15287	GREEN
SPC15141	YELLOW

DISCLAIMER:

ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES:

Unless Otherwise Specified .X ±0.2 [0.008] $.XX \pm 0.12 [0.005]$

DRAWN BY:	DATE:
EKLAS ODISH	03/21/06
CHECKED BY:	DATE:
THOMAS LEE	05/15/06
APPROVED BY:	DATE:
HISHAM ODISH	05/15/06

DRAWING TITLE:

RoHS Compliant ADAPTER KIT, DB25M TO RJ45

_				,	
	SIZE	DWG.	NO.	ELECTRONIC FILE	T
	Α		TA-692	TA-692.DWG	

SCALE: NTS U.O.M.: mm [INCHES] SHEET: 1 OF 1

REV