

Jointed hose system with magnetic base

COOL-LINE® system

ARIANA

Application:

For use on all machines without integrated coolant supply or to extend existing coolant supplies.

Execution:

- With metal ball valve to regulate coolant flow
- Suitable for higher coolant pressure in CNC machines
- Universal push-fit system with various nozzles, branch pieces and screw fittings
- With interchangeable, separate plastic segments
- Can be shortened or extended as desired
- Max. 6 bar operating pressure
- Flow rate approx. 15 l/min

Advantage:

- Resistant to chemicals and solvents
- Not electrically conductive
- Length and position variable as required
- Coolant supplied precisely where it is needed



Art. no.	18300 635
Brand	ARIANA
Manufacturer Part Number	0219029-1
System design	1/4 inch
Type	Magnetic base set
Outlet diameter	6.35 mm
Coolant hose output direction	Vertical
Composition of set	Magnetic base 90°, 16 x jointed hose modules, round nozzle Ø 6.4 mm, threaded connector 1/4", metal ball valve 1/4", threaded grommet 1/4" for size 13 fabric hose
Gross Weight	0.255 kg
Product Group	575