

LED linkage machine light ROCIA.focus

220-240 V/50/60 Hz

Waldmann **W**

Execution:

- Maintenance-free LED technology with high power LEDs
- Continuous, flicker-free dimmer buttons on lamp head
- Precision-adjustment linkage
- Extremely robust solid metal design
- Integrated power supply and internal cable
- Light colour temperature 5000 K, neutral white
- Black and colourless anodised housing, 3-mm thick safety glass
- LED service life > 60,000 h
- Ref. no. 200 with 10° beam angle (optical) / 5088 to 30,053 lx
- Ref. no. 210 with 40° beam angle (optical) / 3255 to 5600 lx

Delivery:

With 3-m connection line and plug, screw-on foot



Art. no.	56883 210
Brand	WALDMANN
Manufacturer Part Number	113181000-00680167
Power rating	8 W
Arm length	420 mm
IP protection class	IP 65
Gross Weight	3.200 kg
Product Group	4AB

EAN

4013330088187