



1930

L1™

With a long lamp life and extended battery burn time, you won't be left in the dark with the L1™ flashlight. The polycarbonate body is resistant to chemicals, water and corrosion. The convenient tail switch for constant on/momentary is easy to operate. The L1™ is perfect for close quarter use. Packaged with 4 LR 44 1.5V alkaline coin cells, a break-a-way safety lanyard, and colored lens discs to preserve night vision. This handy flashlight offers a lot for its size.

- Built Pelican tough
- Super bright LED beam
- Unconditional Lifetime Guarantee of Excellence
- Security Lanyard



CONFIGURATIONS



1930
Standard

1930M
Merchandiser Display

DIMENSIONS

Length 2.64" (6.7 cm)

MATERIALS

Body Polycarbonate (PC)
O-Ring Ethylene Propylene
Lens Polycarbonate (PC)
Shroud Xenoy
Contact Spring Retainer Phosphore Bronze

COLORS

■ Black ■ High Visibility Yellow

LIGHT SPECS

Lamp Type LED

POWER

Battery Size LR 44

Battery Type	Alkaline
Battery Quantity	4
Batteries Included	yes
Volts	6.0v

WEIGHT

Weight With Batteries	0.9 oz (26 gr)
Weight Without Batteries	0.6 oz (17 gr)
Packaged Weight	0.8 oz (23 gr)

SWITCH






Switch Type	Push Button Tail
Light Modes	On / Off

CERTIFICATIONS

Class I, Division 2
Class II, Division 2
Class I, Division 1
IECEX ia
InMetro

OTHER

Minimum Pack	12
Military	yes
Package Code	C

FL1 STANDARD	HIGH
	12 LUMENS
	4h 15mins
	17m
	70cd
	IPX4

ACCESSORIES

Pelican

23215 Early Ave • Torrance, CA 90505 USA • Phone: (310) 326-4700 • (800) 473-5422 • Fax: (310) 326-3311
sales@pelican.com • www.pelican.com

Document created on 09-17-21