

Pin Strip DIN 41651



FEATURES:

- 2.54 mm x 2.54 mm
- Straight type
- Selective gold plating

SPECIFICATION:

Contact material	Gold-Plated
Gold-Plating Thickness	0.4 ~ 0.6u
Connection principle	Wire-Wire
Gender of contacts	Male
Temperature range	-55 ... +105 °C
Pitch	2.54 mm
Insulation material	PBT, UL 94V-0
Contact resistance	30 mΩ max.
Insulation resistance	5000 MΩ min. at 1000 VDC
Dielectric voltage	1000 VAC RMS for 1 min.
Rated current	3 A

Article Nr.	Contacts	Dim.A	Dim.B	Dim.C
RND 205-00839	10	32 mm	10.1 mm	17.4 mm
RND 205-00840	20	44.7 mm	22.8 mm	30.1 mm
RND 205-00841	26	52.3 mm	30.4 mm	37.7 mm
RND 205-00842	34	62.4 mm	40.6 mm	47.8 mm

