


Fuses 5 x 20

Ceramic Fuses, fast-blow



Fast-blow (F) IEC60127-2/1
 Nickel plated brass end caps
 Sand filled
 UL approved, E492698

SPECIFICATION:

Characteristic (time/current)	Fast-blow
Rated voltage	250 VAC/DC
Type of housing/package/case	Ceramic tube
Dimensions $\phi \times L$	5.2 x 20 mm
Breaking capacity	1500 A@ 250 VAC
Approvals	UL

PRODUCT RANGE:

Art. Nr.	Rated current
RND 170-00030	0.25 A
RND 170-00028	0.315 A
RND 170-00025	0.5 A
RND 170-00023	0.63 A
RND 170-00021	0.8 A
RND 170-00035	1 A
RND 170-00034	1.25 A
RND 170-00032	2 A
RND 170-00031	2.5 A
RND 170-00029	3.15 A
RND 170-00027	4 A
RND 170-00026	5 A
RND 170-00024	6.3 A
RND 170-00022	8 A
RND 170-00033	10 A