

MASI67 INSTALLATION TECHNOLOGY


Distribution 1 x profile- to 3x profile cable

MASI67 distribution boxes

1 × on 3 × profile cable

[Link to Product](#)

Illustration



Product may differ from Image

Approvals



Technical Data

Operating voltage	max. 36 V DC
Total current	max. 8 A
Isolation voltage	AS-Interface/Power: 200 V

General data

Protection	IP67
Mounting method	DIN-rail mountable (EN 60715) or screw fixing
Temperature range	-20...+60 °C (storage temperature -40...+80 °C)
Dimensions H × W × D	90×74×26 mm

Commercial data

country of origin	DE
customs tariff number	85369010
minimum order quantity	1