



Figure similar

TRANSFORMER SITAS; PHASES:1;  
 PN/PN(S6)(KVA):0,68 /3,4; UPRI(V):400+/-5%;  
 USEC(V):230; ISEC(A):2,96; F(HZ):50...60; VECTOR  
 GR./SHIELD WNG.:II0 /0; TA/ISOKL:40 /B; IP23; TYPE  
 OF TERMINALS:SCREW/TAB CONNECTION;  
 INSTALLATION:SCREW; EN 61558-2-1, -2-2, -2-4  
 >CONTROL CIRCUIT TRANSFORMER< >ISOLATION  
 TRANSFORMER<

General technical data:

Product designation		transformer SITAS
product brand name		SIDAC
Operating apparent output Rated value	V·A	680
Efficiency		0.93
Connection method for transformers		II0
Certificate of suitability		CE
Product function		
<ul style="list-style-type: none"> <li>• Temperature monitoring</li> <li>• Insulation monitoring</li> <li>• Short-circuit and overload proof</li> </ul>		No No No
Number of shielding windings		0
Short-term vector power	V·A	3 400
Relative short-circuit voltage	%	3.17

Inputs:

Phase number of the inputs		1
Input voltage		
<ul style="list-style-type: none"> <li>• _1 Rated value</li> <li>• _2 Rated value</li> <li>• _3 Rated value</li> </ul>	V V V	420 400 380
Electrical input frequency		
<ul style="list-style-type: none"> <li>• minimum</li> <li>• maximum</li> </ul>	Hz Hz	50 60

Outputs:

Phase number of the outputs		1
Output voltage		
• _1 Rated value	V	230
Electrical output frequency		
• maximum	Hz	60
• minimum	Hz	50

#### Ambient conditions:

Thermal class acc. to IEC 60085		B
Ambient temperature Rated value	°C	40
Protection class IP		IP23

#### Mechanical data:

Type of electrical connection		
• at output for main current circuit		screw-type terminals / tab terminals
• at input for main current circuit		screw-type terminals / tab terminals
Mounting type		screws
Construction form of the iron core		EI 150/65
Width	m	0.244
Height	m	0.245
Depth	m	0.23

#### Certificates/ approvals:

General Product Approval

Shipping Approval

other



[other](#)

#### Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<http://www.siemens.com/industrymall>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=4AM55425AT100FC0>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/4AM55425AT100FC0>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=4AM55425AT100FC0&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=4AM55425AT100FC0&lang=en)

last modified:

15.01.2015