



Cut

Abrasion Protection



Medium Duty

Ultralight abrasion-resistant gloves that offer barehand comfort, dexterity and protection

- **Optimized usability:** The Ansell HyFlex® 11-727's light, barehanded feel, tailored fit and breathable fabric make for consistently comfortable PPE gloves
- **Advanced durability:** ANSI- and EN-certified, HyFlex® 11-727 industrial working gloves remain resilient against abrasion over time
- **Technical underpinnings:** Integrated INTERCEPT™ Cut Resistance Technology prevents workplace injuries
- **Enhanced dexterity:** The 11-727's acute fingertip sensitivity makes for deft, precise hand protection and secure handling
- **Heightened grip:** HyFlex® 11-727 safety gloves also benefit from secure grip for handling dry or slightly oily components
- **Improved practicality:** The 11-727 model is also sold in vend pack form, allowing for convenient replenishment



Industries

- Automotive
- Machinery and Equipment
- Metal fabrication
- Chemical
- Automotive Aftermarket
- Emergency Medical Services
- Utilities
- Warehousing

Applications

- Handling metal sheets & panels
- Handling parts with sharp, rough edges
- Final assembly
- Handling materials with sharp or rough edges
- Assembly & inspection of components
- Applying finish to materials, products
- Maintenance
- Opening furnaces draining pumps valves or lines and crackers BTX process
- Lock smith

HyFlex®

ADVANCED MECHANICAL PROTECTION

11-727

A unique balance of comfort, durability and protection

Key Features

- **Lightweight fabric and seamless liner:** For a flexible, tailored fit
- **Certified durability:** EN- and ANSI-recognized abrasion resistance
- **INTERCEPT™ Cut Resistance Technology:** Ensuring workplace safety

Vulcanization Chemical Accelerators

- Natural rubber proteins (in knitwrist elastic)

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

Performance Standards & Regulatory Compliance

REACH Compliant



Technologies



Specifications

| BRAND STYLE | DESCRIPTION | Gauge | SIZE | LENGTH | COLOR | PACKAGE |
|----------------|---|-------|--------------------|-------------------------------|-------|--|
| HyFlex® 11-727 | Finishing: Palm Coated Coating Material: Polyurethane Liner Material: HPPE, Nylon, Spandex Cuff Style: Knitwrist | 15 | 6, 7, 8, 9, 10, 11 | 195-276 mm; 7.67-10.86 inches | Grey | • 12 pairs in a bag; 12 bags in a carton |

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 210
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Australia

Ansell Limited
Level 3,678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2021 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

