



HH-S120F010-3528

- Warm White
- Neutral White
- Cold White
- Amber
- Red
- Green
- Blue




## FEATURES

- Mercury free, no UV or IR emissions.
- DC12V
- 9.6watts/m
- 5000Hrs LED life time
- Dimmable
- CE,Rohs,UL,cUL

## SPECIFICATIONS

Length	5 meters/Roll
Power	9.6watts/m
Width	10mm
LED Qty	120LED/m
Input Voltage	12VDC
Lumen	6-7lm/LED
PCB	2OZ
CRI	80+
Waterproof	IP20/IP65/IP67

## STRUCTURE



Long life span 50,000 hours	12 VDC	Cut into 3 segments
5m	120°	3 YEARS WARRANTY