

Product information

98 37 5/8"

- For imperial hexagonal head screws
- Basic tool chrome-plated
- With double-hex
- Chrome Vanadium steel

12-Point Socket

With internal square 3/8"

IEC 60900 DIN EN 60900



⚠ 1000 V 

General

Article No.	98 37 5/8"
EAN	4003773020691
Weight	51 g
Dimensions	46 x 25 x 25 mm
Standard	DIN EN 60900 IEC 60900
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details

Square drive	3/8 Inch
Ø of effective tool side d max.	26.2 mm
Width across flats S	5/8 Inch

technical change and errors excepted