# Woodhead<sup>®</sup> Haztex<sup>®</sup> High-Output LED Haz-Duty Light

Developed for harsh environments where uptime and safety are critical, the Wodhead® Haztex® High-Output LED Haz-Duty Light utilizes an integral LED light engine to provide unmatched durability and light output in a portable hazardous-location rated fixture

## **Features and Benefits**

Integral LED Light Engine	Delivers extreme durability for use in the most hazardous of conditions. Eliminates any chance for failure as the light source cannot be unscrewed or unmated
High-Output LED	Provides 15% more luminosity and ten times more lamp life than a 100W incandescent bulb.
20W Power Consumption	Reduces power-infrastructure costs by requiring smaller generators, smaller wire sizes and fewer receptacles. Generates less heat for more effective usage in environments that are often very hot already
Pre-installed LED	Eliminates the cost and time needed for lamp installation and replacement. Creates a "plug and play" solution for hazardous-environment lighting

## **Applications**

### Industrial – Oil and Gas

Petrochemical Plant Shut Downs Painting and Chipping Tank and Vessel Inspections Utilities



Petrochemical Plant

# **Product Overview**

Integral solid-state LED light engine makes this fixture extremely rugged

High-quality Samsung LED's utilize driverless technology; run on 120VAC

Frosted tempered glass globe helps to diffuse the light and soften "hotspots" typical with some LED fixtures



Woodhead® Haztex® High-Output Haz-Duty LED Handlamp 61450



# molex

# Woodhead<sup>®</sup> Haztex<sup>®</sup> High-Output LED Haz-Duty Light



#### **Specifications**

REFERENCE INFORMATION

UL File No.: E30252 (cULus Listed)

Hazardous Locations: Class I, Division I, Groups C and D Class II, Division I, Groups F and G Class I, Zone 1, Group IIB Temperature Rating: T4

#### ELECTRICAL

Voltage (max.): 120V AC Voltage with Plug: 120V AC Power draw (max): 20W Plug (for fixtures with cable): NEMA 5-15 (ordinary location rated)

#### ENVIRONMENTAL

NEMA Rating: NEMA 4X

#### **PHYSICAL** Switch: No Construction: Aluminum with Nylon handle Fixture Lumens: 750

**NOTE:** Fixtures rated at 12V include an in-line driver to step down the 120V supply voltage to 12V or less. The driver enclosure must remain outside the hazardous environment.

#### **Ordering Information**

Woodhead No.	Order No.	Cord Length	Cord Type	Fixture Voltage
61450	130104-0082	N/A	N/A	
61450A163	130104-0086	25		
61450B163	<u>130104-0087</u>	50	16/3 SOOW	
61450D163	130104-0088	100		120V
61450A143	130104-0083	25	-	
61450B143	<u>130104-0084</u>	50		
61450D143	<u>130104-0085</u>	100	14/3 SOOW	
1655-12A	130105-0082	25		12V
1655-12B	130105-0083	50		12V

#### www.molex.com/link/woodheadlighting.html