

166-90130

Article Number: 166-90130



Description: HelaGuard Non-Metallic IP65 Fitting, 90-Elbow, NPT Thread, 0.75" Dia, PA66, Black, 10/pkg

Base Data	Local Order Number	166-90130
	Type	PSR075-90-0750
	Color	Black (BK)
	Features and benefits	<ul style="list-style-type: none"> • External NPT thread provides a secure connection. • Twist-on installation makes future access fast and easy. • Internal spigot design helps ease threading of fitting onto conduit. • All-around "teeth" attach firmly to conduit and deliver a high extraction force. • Durable nylon material has high resistance to salts, oils, weak acids and solvents. • IP65 rating for protection against wind, dirt and low pressure jets of water from all directions.
	Quantity Per	bag
	Product Description	Compression fittings feature a twist-on design for easy installation and future access. Constructed of a very durable nylon material with a high resistance to salts, oils, weak acids and solvents. Fits HelaGuard non-metallic conduits and tubing.
	Short Description	HelaGuard Non-Metallic IP65 Fitting, 90-Elbow, NPT Thread, 0.75" Dia, PA66, Black, 10/pkg
	Product Dimensions	Length L (Imperial)
Length L (Metric)		63mm
Bore Diameter (Imperial)		0.75"
Bore Diameter (Metric)		19.0mm
Clearance Hole Diameter (Imperial)		1.039"
Clearance Hole Diameter (Metric)		26.4mm
Thread Length (Imperial)		0.59"
Trade Size		3/4 "
Outside Diameter D (imperial)		1.65"
Outside Diameter D (metric)		42mm
Nominal Diameter (Imperial)		3/4"
Nominal Diameter (Metric)		25mm
Thread Length (metric)		15mm

166-90130



Material and Specifications		
	Material	Polyamide 6.6 (PA66)
	Material Shortcut	PA66
	Flammability	UL 94 V2
	Operating Temperature	-40°F to +248°F (-40°C to +120°C)
	ROHS Compliant	Yes
	UL Recognized (US and Canada)	Yes
	UL Recognized (US)	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	10
	Package Quantity (Metric)	10Pieces
	Customs Number(Schedule B)	3926909987