



## Shape

### KPEG353 KPEG353H



Model Number	KPEG353	KPEG353H
Rated Frequency (Hz)	2,800 ± 500	
Operating Voltage Range (VDC)	3 ~ 28	7 ~ 18
Current Consumption (mA)	Max. 8@12VDC	Max. 15@12VDC
Sound Pressure Level (dB)	Min. 81dB@30cm / 12VDC	Min. 93dB@30cm / 12VDC
Tone	Slow Pulse@12VDC (1.5Hz±20%)	Slow Pulse@12VDC (1.2Hz±20%)
Operating Temperature (°C)	-30 ~ +85	
Storage Temperature (°C)	-40 ~ +95	
Weight (Gram)	14.6	
Material	ABS UL-94 1/16" HB High Heat (Black)	

# Dimension




Tol :  $\pm 0.5$  Unit : mm

# Characteristic

## KPEG353

at 30cm



## KPEG353H

at 30cm

