

Product data sheet

Item No. 92.238.1004.1

Cable assembly GST18I3K1-S 25 10SW

geis® Connection cable male - free end; length: 1m; type GST18I3; 3-pole; 250 V / 20 A; colour of coding: black with black strain-relief; cable: H05VV-F 3G2,5, colour: black



Item No.	92.238.1004.1
EAN	4015573356672
Order Unit	50 Piece(s)

Certificates / Approvals



Technical data

General

Rated current	20 A
Rated voltage	250 V
Rated impulse voltage	4 kV
Pollution degree	2
Mechanical coding	Code 1
Interlockable	Yes
Color of coding/ contact carrier	Black
Marking of poles	
Color of housing inclusive strain relief	Black

Model

Number of poles	3
Nominal cross section conductor	2.5 mm ²
Degree of protection (IP)	IP40
Wire strip length	9 mm
sheath strip length	37 mm
Preparation of conductor ends	Ultrasonically compressed wire ends
Cable type	H05VV-F



Cable colour	Black
Cable diameter	10.2 mm
Version of cable	Male - free end
Type of cord set	Connection cable
Version cable end 1	GST18i3 plug
Version cable end 2	Free end

Material

Surface finish	Tin-plated
Halogen free	No
Continuous temperature of cable	70 °C
Insulation components continuous temperature	100 °C

Dimensions

Total length	1 m
--------------	-----

Technical drawing

.F	Farbe colour	Codierung *X* Stecker male	Kabelfarbe cable colour
.1	schwarz black	L R N	schwarz black
.2	weiß white	L R N	weiß white
.3	grau grey	L R N	schwarz black
.5	rot red	L R N	schwarz black

Teile-Nr. part-no.
 92.238.XX04.F XX in dm-Schritten 92.238.1004.1 = 10dm/L= 1000mm
 U2.238.XX04.F XX in m-Schritten U2.238.1204.1 = 12 m/L=12000mm

Typ/type: GST1813K1-S 25
 SW = schwarz/black
 WS = weiß/white
 GR01 = grau/grey
 RT03 = rot/red

Weitere Daten siehe Katalog
 further data see catalog

01-PEM-08-910