

Electro-hydraulic compact pumps



Application:

For portable use on single-acting cylinders.

Execution:

- Operating pressure of 700 bar.
- Equipped with an adjustable pressure limiting valve. The pump is configured for intermittent operation (thermal safety switch). The operating time depends on the respective pressure.
- With oil filling
- Wired remote operation of motor as standard (24 V safety voltage). 230 V single phase motor connection.

Delivery:

1x ENERPAC electro-hydraulic compact pump PUJ 1200 E.



Art. no.	29716 120
Brand	ENERPAC
Manufacturer Part Number	PUJ1200E
Model	PUJ-1200 E
Valve design	3/2-way
Feed volume under low pressure at 14 bar	3.3 l/min
Feed volume under high pressure at 700 bar	0.328 l/min
Continuous operating pressure	Depending on load
Effectibe oil content	1.9 l
Tank contents	4 l
Connection thread	NPTF 3/8 inch - 18
Gross Weight	0.490 kg
Product Group	258