

**NTC - Temperature sensor with aluminium sleeve**  
watertight



**Application:**

The temperature sensor with aluminium sleeve and flat tip is suitable for measurements in liquids and paste-like media as well as for air temperature measurements. For continuous measurements, the temperature sensor can be fixed to the measuring location. Only a clip or PG screw connection (not included in the scope of delivery) is required for this purpose.



Art. no.	46108 340
Brand	TESTO
Manufacturer Part Number	0628 7503
Sensor type	NTC
Probe type	Surface probe
Min./max. temperature measuring range	-30 to 90 °C
Accuracy temperature	+/- 0.2°C at 0 to +70°C, +/- 0.5°C (remaining measuring range)
Response time sensor	12 s
Diameter probe tube	6 mm
Length sensor tube	40 mm
Cable length	2.4 m
IP protection class	IP 65
Material of housing	Plastic
Gross Weight	0.110 kg
Product Group	4CF

**EAN**

4029547006777