

PRODUCT DATASHEET HQI-T 1000 W/D

POWERSTAR HQI®-T 1000...2000 W | Metal halide lamps for enclosed luminaires



Areas of application

- Factories and workshops
- Sports halls and multi-purpose halls
- Industrial installations
- Airports
- Docks and port facilities
- Marshaling yards, container transshipment facilities
- Approved only for use in enclosed luminaires
- Outdoor applications only in suitable luminaires

Product benefits

- High efficiency
- E40 screw base for simple lamp handling
- UV values significantly below the maximum permitted thresholds to IEC 61167 thanks to UV filter

Product features

- POWERSTAR® quartz technology
- Light colors: neutral white (N), daylight (D)



TECHNICAL DATA

Electrical data

Nominal wattage	1000 W
Nominal voltage	130 V
Ignition voltage	4.0/5.0 kVp ¹⁾
Nominal current	8.6 A
PFC capacitor at 50 Hz	85 μF

¹⁾ Minimum / Maximum

Photometrical data

Luminous flux	85000 lm
Luminous efficacy	86 lm/W
Color temperature	7250 K
Color rendering index Ra	81
Light color	872
Rated LLMF at 2,000 h	0.71
Rated LLMF at 4,000 h	0.58
Rated LLMF at 6,000 h	0.47
Rated LLMF at 8,000 h	0.35
Rated lamp efficacy (standard co.)	82 lm/W
UV protection	Yes

Dimensions & Weight

Overall length	345.00 mm
Length	345.00 mm
Light center length (LCL)	220,0 mm
Diameter	76 mm
Product weight	412.4 g

Temperatures & operating conditions

Maximum permitted outer bulb temperature	500 °C
Maximum permitted base edge temperature	250 °C

Lifespan

Lifespan	9000 h



Rated lamp survival factor at 2,000 h	0.98
Rated lamp survival factor at 4,000	0.89
Rated lamp survival factor at 6,000	0.76
Rated lamp survival factor at 8,000 h	0.59
Lifespan B50	9000 h

Additional product data

Base (standard designation)	E40
Mercury content	60.0 mg
Design / version	Clear
Product remark	Not for general lighting

Capabilities

Dimmable	No
Burning position	p30
Enclosed luminaire required	Yes
Hot restart	No

Certificates & Standards

Energy consumption	1155.00 kWh/1000h
--------------------	-------------------

Country-specific categorizations

ILCOS	MT/UB-1000/972-H/E/SL-E40-76/345/H
Order reference	HQI-T 1000W/D E

DOWNLOAD DATA

	DOWNLOAD DATA
POF	User instruction
POF	Certificates
POF	Certificates
POF	Declarations of conformity

LOGISTICAL DATA

Product code	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Gross weight	Volume
4008321527035	Round wrap 1		485.00 g	
4008321527042	Shipping box 6	229 mm x 440 mm x 300 mm	3484.00 g	30.23 dm ³

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

DISCLAIMER

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.

