

DESIGN KIT

WE-HCI SMD Flat Wire High Current Inductors



1030		1040		1050	
744 323 020	744 323 120	744 355 215	744 355 220 0	744 325 016	744 325 240
L: 0.2 μ H	L: 1.2 μ H	L: 0.15 μ H	L: 2.0 μ H	L: 0.16 μ H	L: 2.4 μ H
I_{R^*} : 22 A	I_{R^*} : 12 A	I_{R^*} : 25 A	I_{R^*} : 11 A	I_{R^*} : 25 A	I_{R^*} : 14 A
I_{sat} : 50 A	I_{sat} : 15 A	I_{sat} : 60 A	I_{sat} : 13 A	I_{sat} : 58 A	I_{sat} : 17 A
R_{DC} : 0.82 m Ω	R_{DC} : 6.6 m Ω	R_{DC} : 0.58 m Ω	R_{DC} : 7.3 m Ω	R_{DC} : 0.51 m Ω	R_{DC} : 4.75 m Ω
744 323 033	744 323 150	744 355 230	744 355 228 0	744 325 040	744 325 330
L: 0.33 μ H	L: 1.5 μ H	L: 0.3 μ H	L: 2.8 μ H	L: 0.4 μ H	L: 3.3 μ H
I_{R^*} : 18 A	I_{R^*} : 12 A	I_{R^*} : 22 A	I_{R^*} : 9.5 A	I_{R^*} : 24 A	I_{R^*} : 12 A
I_{sat} : 36 A	I_{sat} : 18 A	I_{sat} : 35 A	I_{sat} : 11 A	I_{sat} : 37 A	I_{sat} : 15 A
R_{DC} : 2.17 m Ω	R_{DC} : 6.6 m Ω	R_{DC} : 1.1 m Ω	R_{DC} : 10.6 m Ω	R_{DC} : 0.67 m Ω	R_{DC} : 5.9 m Ω
744 323 056	744 323 220	744 355 256	744 355 243 0	744 325 072	744 325 420
L: 0.56 μ H	L: 2.2 μ H	L: 0.56 μ H	L: 4.3 μ H	L: 0.72 μ H	L: 4.2 μ H
I_{R^*} : 18 A	I_{R^*} : 9.0 A	I_{R^*} : 20 A	I_{R^*} : 8 A	I_{R^*} : 22 A	I_{R^*} : 11 A
I_{sat} : 33 A	I_{sat} : 15 A	I_{sat} : 30 A	I_{sat} : 8 A	I_{sat} : 35 A	I_{sat} : 14 A
R_{DC} : 2.17 m Ω	R_{DC} : 11.38 m Ω	R_{DC} : 1.61 m Ω	R_{DC} : 14.1 m Ω	R_{DC} : 1.3 m Ω	R_{DC} : 7.1 m Ω
744 323 068		744 355 210 0	744 355 256 0	744 325 120	744 325 550
L: 0.68 μ H		L: 1.0 μ H	L: 5.6 μ H	L: 1.2 μ H	L: 5.5 μ H
I_{R^*} : 14 A		I_{R^*} : 16 A	I_{R^*} : 6.7 A	I_{R^*} : 20 A	I_{R^*} : 10 A
I_{sat} : 21 A		I_{sat} : 20 A	I_{sat} : 7.5 A	I_{sat} : 25 A	I_{sat} : 12 A
R_{DC} : 4.79 m Ω		R_{DC} : 3.3 m Ω	R_{DC} : 20.6 m Ω	R_{DC} : 1.8 m Ω	R_{DC} : 10.3 m Ω
744 323 100		744 355 215 0		744 325 180	744 325 650
L: 1.0 μ H		L: 1.5 μ H		L: 1.8 μ H	L: 6.5 μ H
I_{R^*} : 14 A		I_{R^*} : 14 A		I_{R^*} : 16 A	I_{R^*} : 8.4 A
I_{sat} : 21 A		I_{sat} : 17 A		I_{sat} : 18 A	I_{sat} : 10 A
R_{DC} : 4.79 m Ω		R_{DC} : 5.3 m Ω		R_{DC} : 3.5 m Ω	R_{DC} : 12.5 m Ω
					744 325 780
					L: 7.8 μ H
					I_{R^*} : 8 A
					I_{sat} : 9.5 A
					R_{DC} : 13.6 m Ω
					744 325 100 0
					L: 10 μ H
					I_{R^*} : 7.2 A
					I_{sat} : 8.5 A
					R_{DC} : 16.3 m Ω
					744 325 160 0
					L: 16 μ H
					I_{R^*} : 5 A
					I_{sat} : 6.5 A
					R_{DC} : 35.5 m Ω

EMC COMPONENTS | INDUCTORS | TRANSFORMERS | RF COMPONENTS | CIRCUIT PROTECTION | EMC SHIELDING MATERIAL | CONNECTORS | SWITCHES | ASSEMBLY TECHNIQUE | POWER ELEMENTS

Important information: Würth Elektronik's design kits contain reference components. These components correspond with the current product development status on the day of supply. Exchange of the reference components to components with up-to-date product development status is not carried out automatically. No liability is taken for the use of these reference components. Therefore, please request new samples prior to releases for series production and product release.

Please check datasheets on www.we-online.com for specifications. Würth Elektronik eiSos GmbH & Co. KG, EMC & Inductive Solutions. © 2011

www.we-online.com

All products
in stock!