

FEATURES

- SVGA Source
- HDMI Display
- 26cm Cable
- USB Power Cable (1mtr)
- 3.5mm Audio Cable (58cm)
- 1920 x 1080P @ 60Hz
- HDCP 1.2

RS PRO 26cm SVGA Male to HDMI Female Adaptor + Audio & USB Power

RS Stock No: 195-4344



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description


The RS PRO VGA to HDMI converter can convert the analogue signal coming from your PC into a digital HDMI signal. This allows you to plug your older laptop or desktop computer into a modern HD television. You can not only enjoy a high-definition image but also audio from the 3.5mm stereo socket. Power is provided from the included USB cable; simply plug this into your computer. No external power adapter is needed.

General Specifications

| | |
|------------------------------|----------------------------------|
| Connector A | VGA/SVGA/HD15 Male (Source Only) |
| Connector B | HDMI Female (Display Only) |
| Length | 26cm |
| Outer Sheath Material | PVC |
| Sheath Colour | Black |

Approvals

| | |
|-------------------------------------|--------------------|
| Declarations | CE UKCA REACH ROHS |
| Hazardous Area Certification | CE UKCA REACH ROHS |
| Standards Met | CE UKCA REACH ROHS |



| | | | | | |
|---|--|-------------|---|-----|---|
| 9 | | 3.5mm Male | 3.5mm stereo male | PCS | 1 |
| 8 | | PVC | PVC 45PA Black | PCS | 1 |
| 7 | | HDMI Female | HDMI Female / Nickel plated | PCS | 1 |
| 6 | | Front Bezel | ABS front bezel | PCS | 1 |
| 5 | | Shell | Aluminium alloy black | PCS | 1 |
| 4 | | Back Bezel | ABS back bezel | PCS | 1 |
| 3 | | Cable | VGA cable 150mm / 3.5mm 600mm | PCS | 1 |
| 2 | | Hood | ABS black / black inner mould | PCS | 1 |
| 1 | | VGA Male | Nickel plated shell / gold plated terminals | PCS | 1 |

| | |
|-------------|------|
| P2 | PCBA |
| GND | GND |
| grey | 14 |
| green | R |
| blue | L |
| Light blue | 3 |
| Light green | 2 |
| pink | 1 |
| blue | 15 |
| brown | 12 |
| red | 9 |
| black | 13 |
| orange | GRN |
| GND | GRN |

