

MILAN S.r.l. a socio unico

**Head Office – Export department:**  
 Viale Europa, 74  
 20090 Cusago (MI) Italy  
 T. +39 02 9039.4556-4158  
 F. +39 02 9039.4551  
 www.taskercables.com

**Ufficio Commerciale e Centro Distribuzione**  
 Viale Europa 72 Strada F12  
 20090 Cusago (MI) Italy  
 T. +39 02 9039.0037-0059  
 F. +39 02 9039.0049  
 www.tasker.it



# Technical Datasheet

## tasker® C202 Balanced Microphone Cable



A	B	C	D
---	---	---	---

**CATEGORY**    **Balanced Microphone Cable** (See Audio Catalogue)

- A:**     Black Soft **PVC** Sheath. Outer cable Diam. Ø: 3,00 (±0,10) mm.
- B:**     Shielding in O.F.C. tinned copper spiral covering 100%.
- C:**     Core Insulation with PVC, colored one Red and one White.  
Diam. Ø: 0,90 (±0,10) mm.
- D:**     O.F.C. tinned copper formation 12x0,10 mm.  
Nom. Cross section 2x0,08 mm<sup>2</sup>.

**MARKING**    **tasker® C 202 2x0,08 mm<sup>2</sup> O.F.C. Balanced Mini Microphone Cable**  
**CUSTOM**    This product is also available in **L.S.Z.H., PE, PUR**, with or without **Steel Armor**.

**Cable Properties**

<b>Conductor Resistance</b>	210 Ω/Km ± 5%
<b>Capacity Core/Core</b>	170 pF/mt
<b>Capacity Core/Shield</b>	310 pF/mt
<b>Max Rated Voltage</b>	49 V
<b>Operative Temperature</b>	-15/+70°C

<b>USE</b>	<b>X</b>	Indoor	Interno Edificio	<b>INSTALLATION</b>	<b>X</b>	Fixed	Fissa	<b>INFORMATION</b>	<b>X</b>	RoHS2 Compliant
<b>Impiego</b>	<b>X</b>	Outdoor Limited	Esterno Limitato	<b>Posa</b>	<b>X</b>	Flexible Limited	Flessibilità limitata	<b>Informazioni</b>	<b>X</b>	Ver. C / 14.06.16
		Outdoor Direct Burial	Esterno Interrato		<b>X</b>	Dynamic (Drag Chain)	Mobile in Catena			
		.....	.....			Dynamic (Torsion)	Mobile in Torsione			.....