

Stranded Wires

with PVC Insulation, H07V-K



Class 5 flexible copper conductor

Fixed temperature rating -30°C to +70°C

For use in the switch control, relay and instrumentation panels, as internal connectors, motor starters and controllers

SPECIFICATION:

Wire Code	H07V-K
Cable type	Stranded
Shielding	unshielded
Conductor	Copper
Halogen-free	No
Conductor insulation	PVC
Original packaging	100 m
Rated voltage	450/750 V
Temperature range	-5...+70 °C

PRODUCT RANGE:

Art. Nr.	Colour	Cross-section	∅ Sheath
RND 475-00120	black	1.50 mm ²	2.9 mm
RND 475-00121	blue	1.50 mm ²	2.9 mm
RND 475-00122	brown	1.50 mm ²	2.9 mm
RND 475-00123	green-yellow	1.50 mm ²	2.9 mm
RND 475-00124	grey	1.50 mm ²	2.9 mm
RND 475-00125	red	1.50 mm ²	2.9 mm
RND 475-00126	white	1.50 mm ²	2.9 mm
RND 475-00127	yellow	1.50 mm ²	2.9 mm
RND 475-00128	orange	1.50 mm ²	2.9 mm
RND 475-00129	pink	1.50 mm ²	2.9 mm
RND 475-00130	violet	1.50 mm ²	2.9 mm
RND 475-00131	green	1.50 mm ²	2.9 mm
RND 475-00132	black	2.50 mm ²	3.6 mm
RND 475-00133	blue	2.50 mm ²	3.6 mm
RND 475-00134	brown	2.50 mm ²	3.6 mm
RND 475-00135	green-yellow	2.50 mm ²	3.6 mm
RND 475-00136	grey	2.50 mm ²	3.6 mm
RND 475-00137	red	2.50 mm ²	3.6 mm
RND 475-00138	white	2.50 mm ²	3.6 mm
RND 475-00139	yellow	2.50 mm ²	3.6 mm
RND 475-00140	orange	2.50 mm ²	3.6 mm
RND 475-00141	pink	2.50 mm ²	3.6 mm
RND 475-00142	violet	2.50 mm ²	3.6 mm
RND 475-00143	green	2.50 mm ²	3.6 mm
RND 475-00144	black	4.00 mm ²	4.1 mm

Art. Nr.	Colour	Cross-section	∅ Sheath
RND 475-00145	blue	4.00 mm ²	4.1 mm
RND 475-00146	brown	4.00 mm ²	4.1 mm
RND 475-00147	green-yellow	4.00 mm ²	4.1 mm
RND 475-00148	grey	4.00 mm ²	4.1 mm
RND 475-00149	red	4.00 mm ²	4.1 mm
RND 475-00150	white	4.00 mm ²	4.1 mm
RND 475-00151	yellow	4.00 mm ²	4.1 mm
RND 475-00152	violet	4.00 mm ²	4.1 mm
RND 475-00153	orange	4.00 mm ²	4.1 mm
RND 475-00154	pink	4.00 mm ²	4.1 mm
RND 475-00155	green	4.00 mm ²	4.1 mm
RND 475-00156	black	6.00 mm ²	4.7 mm
RND 475-00157	blue	6.00 mm ²	4.7 mm
RND 475-00158	brown	6.00 mm ²	4.7 mm
RND 475-00159	green-yellow	6.00 mm ²	4.7 mm
RND 475-00160	grey	6.00 mm ²	4.7 mm
RND 475-00161	red	6.00 mm ²	4.7 mm
RND 475-00162	white	6.00 mm ²	4.7 mm
RND 475-00163	yellow	6.00 mm ²	4.7 mm
RND 475-00164	violet	6.00 mm ²	4.7 mm
RND 475-00165	orange	6.00 mm ²	4.7 mm
RND 475-00166	pink	6.00 mm ²	4.7 mm