




EDOGH050MSS00.7E05(M16)

Connection technology



1: O-ring

**Product characteristics**

**Adapter socket**

M16 - M12

**Electrical data**

**Electrical design**

AC/DC

**Operating voltage** [V]

125 AC/DC

**Environment**

**Ambient temperature** [°C]

-25...85

**Protection**

IP 68

**Mechanical data**

**Housing materials**

diecast zinc nickel-plated

**Weight** [kg]

0.025

**Electrical connection**

**Connection**

PVC cable / 0.7 m; 4 x 0.25 mm<sup>2</sup> + 1 x 0.5 mm<sup>2</sup>

**Wiring**

**Core colours**


BK black

BN brown

BU blue

GN/YE green/yellow

WH white



1	BN
2	WH
3	BU
4	BK
5	GN/YE

**Remarks**

**Pack quantity**

[piece]

1