


RMI 11/230V AC OUTPUT RELAY

IN: 230 VAC/DC - OUT: 250 VAC/DC / 8 A

1 relay; 1 NO/NC contact
8 A
230 V AC/DC
Screw terminals

[Link to Product](#)

Illustration



Product may differ from Image

Utilization category

AC-15	3 A (24/110/230 V AC)
AC-1	8 A (24/110/230 V AC)
DC-13	2.5 A (24 V DC); 0.4 A (110 V DC); 0.3 A (230 V DC)

Input

Connection voltage - current	230 VAC/DC (195...253 VAC/DC) - 5mA
LED display	LED (red)

General data

Mech./ elect. life	20.000.000 switching cycles/load dependent
Test isolation voltage	6 kV
Mounting method	DIN-rail mountable TH35 (EN 60715)
Temperature range	-25...+60 °C (storage temperature -40...+80 °C)

Output

Switching voltage	max. 250 V AC/DC
Switching current per output	max. 8 A
Min. load current	1 mA
Power rating (voltage dependent)	max. 2000 VA/240 W
Switching frequency	max. 0.1 Hz (with load)
Contact material	Ag Ni
Energize/release/contact bounce time	10/15/2 ms

Commercial data

country of origin	CZ
customs tariff number	85364900
minimum order quantity	1