



FXX*1)PA-K700

e.g. F15PA-K700

*1) xx No. of contacts 09, 15, 25 or 37

xx	A [mm]	B [mm]	C [mm]
09	30.8	16.9	25
15	39.1	25.2	33.3
25	53	38.9	47.04
37	69.3	55.3	63.5

Protection standard IP67, 100% checked according to DIN 40050

RoHS compliant

xx	Signal contact	P0 / Brass	AuroPur / AWG 20
2	1 Shell	Brass	tin plated
1	1 Insulator	PBT (-25°C - +70°C)	red
No.	St.	Part	Surface plating/Colour/Class

TITLE		SCALE	
ISO 2768-m	2:1	Measurement without tolerance	
NAME / DATE		sschref	
DRAWN	22-05-2013	A. Denzinger	
CHECKED	22-05-2013		

Waterproof D-Sub Miniature Connector

REV.	DATE	CH.-NO.	DWG.NO.	REPLACEMENT FOR:	PAGES
1			FxxPA-K700		1

