


H0,75/14D GR



Similar to illustration

General ordering data

Type	H0,75/14D GR
Order No.	9019040000
Version	Wire end ferrule, insulated, 10 mm, 8 mm, Grey
GTIN (EAN)	4008190099077
Qty.	500 pc(s).
Packaging	loose

Dimensions and weights

Width	14 mm
Width (inches)	0.551 inch
Net weight	0.08 g

Technical data

Version	insulated
---------	-----------

Wire-end ferrules

Collar diameter (D2)	2.8 mm
Colour code	DIN
Conductor cross-section	0.75 mm ²
Contact surface diameter (D1)	1.2 mm
Contact surface length (L2)	8 mm
L1 in mm	14 mm
Metal sleeve thickness (S1)	0.15 mm

Military designation	T 20A 004 A
Plastic collar thickness (S2)	0.25 mm
Stripping length	10 mm
Wire connection cross section AWG, max.	AWG 18

Downloads

Brochure/Catalogue	CAT 6 TOOLS 15/16 EN
Engineering Data	EPLAN, WSCAD, Zuken E3.S

Classifications

ETIM 3.0	EC000005
ETIM 4.0	EC000005
ETIM 5.0	EC000005
ETIM 6.0	EC000005
UNSPSC	31-16-31-02
eClass 5.1	27-40-02-01
eClass 6.2	27-40-02-01
eClass 7.1	27-40-02-01
eClass 8.1	27-40-02-01
eClass 9.0	27-40-02-01
eClass 9.1	27-40-02-01

Approvals

Approvals




ROHS	Conform
UL File Number Search	E354986

Related products:

Type: H0,75/12 W
Order No.: 0409600000

Version:
Wire end ferrule, insulated, 8 mm, 6 mm, White

Description of article: Wire end ferrule with plastic collar, white




[PDF data sheet](#) [Add to Inquiry List](#)

Type: H0,75/12D GR
Order No.: 9019030000

Version:
Wire end ferrule, insulated, 8 mm, 6 mm, Grey

Description of article: Wire end ferrule with plastic collar, grey




[PDF data sheet](#) [Add to Inquiry List](#)

Type: H0,75/12T HBL
Order No.: 9021030000

Version:
Wire end ferrule, insulated, 8 mm, 6 mm, Light Blue

Description of article: Wire end ferrule with plastic collar, light blue



[PDF data sheet](#) [Add to Inquiry List](#)

Type: H0,75/14 HBL
Order No.: 9021040000

Version:
Wire end ferrule, insulated, 10 mm, 8 mm, Light Blue

Description of article: Wire-end ferrule




[PDF data sheet](#) [Add to Inquiry List](#)

Type: H0,75/14 W
Order No.: 0462900000

Version:
Wire end ferrule, insulated, 10 mm, 8 mm, White

Description of article: Wire end ferrule with plastic collar, white




[PDF data sheet](#) [Add to Inquiry List](#)


Type: H0,75/16 W
Order No.: 9025860000

Version:
Wire end ferrule, insulated, 12 mm, 10 mm, White

Description of article: Wire end ferrule with plastic collar, white



[PDF data sheet](#) [Add to Inquiry List](#)




Type: H0,75/16D GR
Order No.: 9019050000

Version:
Wire end ferrule, insulated, 12 mm, 10 mm, Grey

Description of article: Wire end ferrule with plastic collar, grey

[PDF data sheet](#) [Add to Inquiry List](#)




Type: H0,75/16T HBL
Order No.: 9021050000

Version:
Wire end ferrule, insulated, 12 mm, 10 mm, Light Blue

Description of article: Wire end ferrule with plastic collar, light blue

[PDF data sheet](#) [Add to Inquiry List](#)




Type: H0,75/18 W
Order No.: 9025910000

Version:
Wire end ferrule, insulated, 14 mm, 12 mm, White

Description of article: Wire end ferrule with plastic collar, white

[PDF data sheet](#) [Add to Inquiry List](#)




Type: H0,75/18D GR
Order No.: 9019060000

Version:
Wire end ferrule, insulated, 14 mm, 12 mm, Grey

Description of article: Wire end ferrule with plastic collar, grey

[PDF data sheet](#) [Add to Inquiry List](#)



Type: H0,75/18T HBL
Order No.: 9021060000

Version:
Wire end ferrule, insulated, 14 mm, 12 mm, Light Blue

Description of article: Wire end ferrule with plastic collar, light blue

[PDF data sheet](#) [Add to Inquiry List](#)