



RE471

Epoxy fibre-glass FR4 1.50 mm- Double-sided Cu- Plated through holes (PTH)- Surface chem. Ni/Au with soldering stop mask

- Two universal QFP layouts for various housing sizes and pin numbers: LQFP; PQFP; TQFP Layer 1 24 to 144 pins, 0.50 mm pitch, sq. Layer 2 24 to 144 pins, 0.65 mm pitch, sq.
- Four pin rail rows 2 x 18 pole, basic grid 2.54 mm, borings 1.00 mm Ø
- Size 57.2 x 57.2 mm