

RANA T5 1500 S&S


RANA S 1500 White Bright Louvre 2x49W T5 840

0050566



Product features

- Surface or Suspended T5 luminaire, 1483 x 187 x 47mm, White coated body, Bright Aluminium Reflector 98% reflectivity, 2 x 49W T5 lamps (included), Neutral White 4000K, Electronic Ballast, 110W, 7910lm, LOR 95%, Push-in Connector, IP20, IK07, Glow Wire test 960°C, UGR<21, LM65<1000 cd/m².



UK
CA

PRODUCT OVERVIEW

| | |
|-----------------------------|--|
| Product name | RANA S 1500 White Bright Louvre 2x49W T5 840 |
| Technology | T5 |
| Cap/Base | G5 |
| Housing | Steel |
| Mount | Ceiling surface mounting, Suspended |
| Environment | Interior |
| General application | Education, Hospitality, Office, Retail |
| ETIM Class | EC002892 |
| E-number FI | 4289232 |
| E-number Norway | 3319611 |
| Warranty | 2 years |
| Fixture luminous flux (lm) | 7910 |
| Luminaire efficacy (lm/W) | 72 |
| LOR (%) | 85 |
| Colour temperature (K) | 4000 |
| Light colour | Neutral White |
| CRI (Ra) | 85 |
| Glare control | < 21 |
| Light source included | 0002777 |
| Total power consumption (W) | 110 |
| Electrical protection | Class I |
| Control gear type | Electronic ballast |
| Control gear mounting | Integral |
| Dimmable | No |
| Housing colour | White |
| IP rating | IP20 |
| IK rating | IK07 |
| Product EAN number | 5410288505664 |

RANA T5 1500 S&S

RANA S 1500 White Bright Louvre 2x49W T5 840

0050566

DATA TABLE

General data

| | |
|--|--|
| Product name | RANA S 1500 White Bright Louvre 2x49W T5 840 |
| Technology | T5 |
| Cap/Base | G5 |
| Housing | Steel |
| Mount | Ceiling surface mounting, Suspended |
| Environment | Interior |
| General application | Education, Hospitality, Office, Retail |
| Performance ambient temperature Tq (°C) | 25 |
| ETIM Class | EC002892 |
| E-number FI | 4289232 |
| E-number Norway | 3319611 |
| Warranty | 2 years |

Optical data

| | |
|-----------------------------------|---------------|
| Fixture luminous flux (lm) | 7910 |
| Luminaire efficacy (lm/W) | 72 |
| LOR (%) | 85 |
| Colour temperature (K) | 4000 |
| Light colour | Neutral White |
| CRI (Ra) | 85 |
| Adjustable chromaticity | N |
| Distribution type | Symmetric |
| Glare control | < 21 |

Electrical data

| | |
|--|--------------------|
| Light source included | 0002777 |
| Total power consumption (W) | 110 |
| Mains voltage (V) | 220-240V |
| Electrical protection | Class I |
| Control gear type | Electronic ballast |
| Control gear mounting | Integral |
| Transformer required | Yes |
| Dimmable | No |
| Glow Wire Test (°C) | 960 |
| Energy Efficiency Class (A->G) of contained light source | F |
| Nominal Frequency (Hz) | 50/60Hz |

Physical data

| | |
|------------------------------------|------------|
| Housing colour | White |
| IP rating | IP20 |
| IK rating | IK07 |
| Reflector finish | High-gloss |
| Nominal Product Length (mm) | 1483 |
| Nominal Product Width (mm) | 187 |

RANA T5 1500 S&S


RANA S 1500 White Bright Louvre 2x49W T5 840
0050566

| | |
|-----------------------------|------|
| Nominal Product Height (mm) | 46 |
| Weight (kg) | 4.08 |

Packaging

| | |
|---------------------------------------|----------------|
| Single packaging type | Carton |
| Product EAN number | 5410288505664 |
| Packaging single length / height (cm) | 149.5 |
| Packaging single width (cm) | 5.5 |
| Packaging single depth (cm) | 20.0 |
| DUN14 (outer) | 05410288505664 |
| Units per outer package | 1 |
| Packaging outer length / height (cm) | 149.5 |
| Packaging outer width (cm) | 5.5 |
| Packaging outer depth (cm) | 20.0 |

PHOTOMETRY



TECHNICAL DRAWINGS

| Dimensions | | Length | | | | | | Width | | | | | |
|-------------|--|--------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| | | Side | | | Front | | | Side | | | Front | | |
| Fixing | | 1x20W | 1x35W | 1x50W | 2x35W | 2x50W | 2x35W | 2x50W | 1x40W | 1x60W | 1x80W | 2x60W | 2x80W |
| Length (mm) | | 1183 | 1483 | 1783 | 1183 | 1483 | 1783 | 1183 | 1483 | 1783 | 1183 | 1483 | 1783 |
| Width (mm) | | 167 | 167 | 167 | 167 | 167 | 167 | 167 | 167 | 167 | 167 | 167 | 167 |
| Height (mm) | | 47 | 47 | 47 | 47 | 47 | 47 | 47 | 47 | 47 | 47 | 47 | 47 |
| Fixing | | 1x40W | 2x40W | 2x50W | 2x50W | 2x50W | 2x50W | 2x50W | 2x50W | 2x50W | 2x50W | 2x50W | 2x50W |
| Length (mm) | | 1483 | 1483 | 1783 | 1783 | 1783 | 1783 | 1783 | 1783 | 1783 | 1783 | 1783 | 1783 |
| Width (mm) | | 167 | 167 | 167 | 167 | 167 | 167 | 167 | 167 | 167 | 167 | 167 | 167 |
| Height (mm) | | 47 | 47 | 47 | 47 | 47 | 47 | 47 | 47 | 47 | 47 | 47 | 47 |