

Colossal

COLOSSAL 400 3400LM 830 DALI EM3 WHITE

4061106



Product features

- Large 400 mm diameter circular architectural luminaire, can be surface mounted or suspended, aluminium housing with polycarbonate opal diffuser, 3400 lm, 30W, 113 lm/W, 3000K, CRI 80, 50,000 hours, IP40, IK03, Class 1, 220-240V, Energy class A++, DALI, Emergency 3 hours



PRODUCT OVERVIEW

Product name	COLOSSAL 400 3400LM 830 DALI EM3 WHITE
Technology	LED
Housing	Aluminium
Environment	Indoor
General application	Hospitality
ETIM Class	EC002892
Warranty	5 years
Fixture luminous flux (lm)	3400
Luminaire efficacy (lm/W)	113
Colour temperature (K)	3000
Colour Code	830
Light colour	Warm White
CRI (Ra)	80
Colour Consistency (SDCM)	3
Colour Variation Initial (SDCM)	SDCM3
Beam Angle (°)	100
Photobiological Risk Group	RG0
Luminous flux (emergency) (lm)	170
Total power consumption (W)	30
Electrical protection	Class I
Dimmable	Yes
Dimming method	DALI
LED Flickering Rate	Ultra low (5% or less)
Housing colour	White
IP rating	IP40
IK rating	IK03
Product EAN number	5026524611060

DATA TABLE

General data

Product name	COLOSSAL 400 3400LM 830 DALI EM3 WHITE
--------------	----------------------------------------

Colossal

COLOSSAL 400 3400LM 830 DALI EM3 WHITE
4061106

Technology	LED
Housing	Aluminium
Environment	Indoor
General application	Hospitality
Performance ambient temperature Tq (°C)	25
ETIM Class	EC002892
Warranty	5 years

Optical data

Fixture luminous flux (lm)	3400
Luminaire efficacy (lm/W)	113
Colour temperature (K)	3000
Colour Code	830
Light colour	Warm White
CRI (Ra)	80
Colour Consistency (SDCM)	3
Colour Variation Initial (SDCM)	SDCM3
Beam Angle (°)	100
Photobiological Risk Group	RG0
Luminous flux (emergency) (lm)	170
Emergency duration (h)	3

Electrical data

Total power consumption (W)	30
Mains voltage (V)	220-240V
Electrical protection	Class I
Dimmable	Yes
Dimming method	DALI
Drive current (mA)	333
Glow Wire Test (°C)	650
Nominal Frequency (Hz)	50/60Hz
LED Flickering Rate	Ultra low (5% or less)
Max. Luminaires per 10A C Breaker	21
Max. Luminaires per 13A C Breaker	28
Max. Luminaires per 16A C Breaker	36

Lifetime data

Lifespan L70 B50	60000
Lifespan L80 B20	50000

Physical data

Housing colour	White
IP rating	IP40
IK rating	IK03
Diffuser finish	Opal
Diffuser material	PMMA Acrylic
Nominal Product Length (mm)	400
Nominal Product Width (mm)	400

Colossal COLOSSAL 400 3400LM 830 DALI EM3 WHITE 4061106

Nominal Product Height (mm)	87
Nominal Product Diameter (mm)	400
Weight (kg)	4.8





Packaging

Single packaging type	Carton
Product EAN number	5026524611060
Packaging single length / height (cm)	50.5
Packaging single width (cm)	40.5
Packaging single depth (cm)	10.0
DUN14 (outer)	05026524611060
Units per outer package	1
Packaging outer length / height (cm)	50.5
Packaging outer width (cm)	40.5
Packaging outer depth (cm)	10.0

Safety data

Optimal operating condition (°C)	0-0
----------------------------------	-----

PHOTOMETRY



Colossal

COLOSSAL 400 3400LM 830 DALI EM3 WHITE
4061106

TECHNICAL DRAWINGS

