

Reducing sleeves E1 + E2 with slot

With groove

ORION[®]

Execution:

- Surface hardness 58–60 HRC
- Core strength HV 950 N/mm²
- Hardness depth 0.8 mm ±0.2 mm
- Fully bronzed and precision-ground

Art. no.	22778 238
Brand	ORION
Manufacturer Part Number	22778238
Clamping diameter	50 mm
Clamping diameter 2	40 mm
Collar diameter	45 mm
Length	80 mm
Collar width	3 mm
Clearance	5 mm
Length 2	72 mm
Groove width	17 mm
Gross Weight	0.483 kg
Product Group	2AL



EAN

4053625466160

