

Vertical cabinets with perforated metal plate walls

With 5 vertical pull-outs in 2 heights



Execution:

- Robust design made of 3 mm steel sheet
- Sturdy plastic rollers with needle bearings that withstand heavy loads
- Lockable drawers with labelling space
- Load capacity per drawer 900 kg (option up to 1800 kg on request)
- Can be easily moved by pallet truck when empty
- Perforated metal plate walls with square holes 10 x 10 mm, distance between hole centres 38 mm, and round holes of 5 mm
- Perforated metal plate walls can be used fully from either side
- Other colours deliverable on request

Advantage:

- Permits space-saving storage of tools in a compact format



Art. no.	50049 026
Brand	APFEL
Manufacturer Part Number	2336343
Model	WK 002 set K
Door design	Full-sheet panel
Number of vertical pull-out mechanisms	5 PCS
Vertical pull-out mechanism design	Five perforated panel walls
Load-carrying capacity per pull-out mechanism	900 kg
Height	2140 mm
Width	1040 mm
Depth	1050 mm
Load-carrying capacity	4500 kg
Lock type	Cylinder lock
Material	Sheet steel
Cabinet colour	Anthracite grey RAL 7016
Colour of front	Grey white RAL 9002
Surface	Powder-coated
Gross Weight	550.000 kg
Product Group	586