



## CS 1525 SK

SHRINK INSULATED BUTT SPLICE RED, 36mm

Krymphylsor CS-serien

Material: Förtent koppar

Isolering: Polyamid (PA) nylon med invändigt lim

Krymptemperatur: 120° C

Temperaturområde: -55° C till +125° C

## Product Properties:

<b>Model</b>	UL model
<b>Insulation</b>	Shrink insulation PE
<b>Colour insulation</b>	Red
<b>Sleeve form</b>	Short
<b>Suitable for solid cores</b>	Yes
<b>Suitable for stranded conductors</b>	Yes
<b>Suitable for fine strand conductors</b>	Yes
<b>Suitable for high temperatures (to 650 °C)</b>	No
<b>Suitable for insulated varnish</b>	No
<b>Suitable for round conductors</b>	Yes
<b>Suitable for flat conductors</b>	No
<b>For pull protected connections</b>	No
<b>Voltage level</b>	Up to 600 V
<b>Type of connection</b>	Other

Oil stop/centre bar	No
Surface protection	Tinned
Material	Copper
Packaging	Loose piece
Number of branches	0-0 N/A
Operating temperature	-55-125 °C

### **Dimensions:**

Unit	pcs
Nominal cross section	0,5-1,65 mm <sup>2</sup>
MOQ	100 .

### **Approvals:**

Approved according to CE	Yes
--------------------------	-----

### **Compliance:**

RoHS	RoHS 3 (2015/863)
Conflict minerals	Yes, see report under tab "Documents"
Reach	No SVHC (209 Subs. Jan 2020)

### **Logistic information:**

Barcode	733117611047
Country of origin	DE
Item status	Stock item, normally in stock with reservation for in between sales.
Packaging	Loose piece
Stock code	CS 1525 SK
Taric code	85369010
Unit	pcs
MOQ	100 .