





07 HVP, 07 HVP/T

For High Voltages up to 400V DC




07 HVP



**07 HVP/T
(With Tube)**

Pin Type Coils

Plugable Inductors



Part No	Inductance	f _L	Tol	SRF	DCR	Rated DC Current (A)	
	L (µH)	(kHz)	± (%)	(MHz)	max (Ω)	I _{N max}	I _{sat typ}
07HVP-560K-51	56	1 @ 0.25V	10	5.97	0.13	1.93	1.97
07HVP-101K-51	100	1 @ 0.25V	10	4.42	0.23	1.44	1.60
07HVP-121K-51	120	1 @ 0.25V	10	3.80	0.29	1.14	1.45
07HVP-221K-51	220	1 @ 0.25V	10	3.14	0.52	1.00	1.10
07HVP-271K-51	270	1 @ 0.25V	10	2.60	0.70	0.68	1.00
07HVP-471K-51	470	1 @ 0.25V	10	2.00	1.18	0.58	0.75
07HVP-681K-51	680	1 @ 0.25V	10	1.66	1.57	0.57	0.68
07HVP-821K-51	820	1 @ 0.25V	10	1.45	1.97	0.53	0.59
07HVP-102K-51	1000	1 @ 0.25V	10	1.30	2.57	0.44	0.50
07HVP-122K-51	1200	1 @ 0.25V	10	1.26	2.98	0.34	0.55

Core Material : Ferrite

Revision date : 27 Jul 2015

SPQ :

Packing Form	Taped / Reel
Radial	500 [-51]